


## Accessories

## Zubehör


## Accessoires

## Accessori

## Accesorios

E-Z Clip/Crimp  
O-Ring NippleE-Z Clip/Crimp  
O-Ring NippleE-Z Clip/Crimp  
O-Ring NippleE-Z Clip/Crimp  
O-Ring NippleE-Z Clip/Crimp  
O-Ring Nipple

| Part Number | Hose ND | Hose Size | Tube O.D. mm | A mm | D mm | S Ø mm | Material | O-Ring | Quantity |
|-------------|---------|-----------|--------------|------|------|--------|----------|--------|----------|
| 1F40106-04  | 5       | -4        |              |      | 3,5  | 1,0    |          |        |          |
| 1F40106-06  | 8       | -6        |              |      | 5,5  | 1,0    |          |        |          |
| 1F40106-08  | 10      | -8        |              |      | 8,0  | 1,0    |          |        |          |
| 1F40106-10  | 13      | -10       |              |      | 9,5  | 1,5    |          |        |          |
| 1F40106-12  | 16      | -12       |              |      | 12,0 | 2,0    |          |        |          |
| 1F40106-16  | 19      | -16       |              |      | 15,5 | 2,6    |          |        |          |

E-Z Clip fittings  
Life SaverE-Z Clip Armaturen  
Life SaverE-Z Clip Embouts  
Life SaverE-Z Clip Raccordi  
Life SaverE-Z Clip racores  
Life Saver

| Part Number  | Hose ND | Hose Size | Tube O.D. mm | A mm | D mm | S Ø mm | Material | O-Ring     | Quantity |
|--------------|---------|-----------|--------------|------|------|--------|----------|------------|----------|
| GW1172-0604S | 5       | -4        |              | 28,8 | 22,5 | 6      |          | 1F40106-04 | 1        |
| GW1172-0804S | 5       | -4        |              | 30,7 | 24,4 | 8      |          | 1F40106-04 | 1        |
| GW1172-1004S | 5       | -4        |              | 31,7 | 25,4 | 10     |          | 1F40106-04 | 1        |
| GW1172-0806S | 8       | -6        |              | 46,9 | 50,9 | 8      |          | 1F40106-06 | 2        |
| GW1172-1206S | 8       | -6        |              | 47,9 | 52,9 | 12     |          | 1F40106-06 | 2        |
| GW1172-1008S | 10      | -8        |              | 47,4 | 51,4 | 10     |          | 1F40106-08 | 2        |
| GW1172-1208S | 10      | -8        |              | 47,4 | 51,1 | 12     |          | 1F40106-08 | 2        |
| GW1172-1608S | 10      | -8        |              | 48,9 | 52,9 | 16     |          | 1F40106-08 | 2        |
| GW1172-1210S | 13      | -10       |              | 47,6 | 51,6 | 12     |          | 1F40106-10 | 2        |
| GW1172-1610S | 13      | -10       |              | 47,6 | 51,6 | 16     |          | 1F40106-10 | 2        |
| GW1172-1810S | 13      | -10       |              | 49,1 | 53,1 | 18     |          | 1F40106-10 | 2        |
| GW1172-1212S | 16      | -12       |              | 47,3 | 53,6 | 12     |          | 1F40106-12 | 2        |
| GW1172-1612S | 16      | -12       |              | 47,3 | 53,6 | 16     |          | 1F40106-12 | 2        |
| GW1172-1812S | 16      | -12       |              | 47,3 | 53,6 | 18     |          | 1F40106-12 | 2        |
| GW1172-1816S | 19      | -16       |              | 49,8 | 56,1 | 18,2   |          | 1F40106-16 | 2        |
| GW1172-2216S | 19      | -16       |              | 49,8 | 56,1 | 22,2   |          | 1F40106-16 | 2        |

Other fitting variants can be supplied on request.

Auf Wunsch sind weitere Armaturvarianten lieferbar.

Su richiesta sono disponibile tutte le varianti di raccordo.

A petición están disponibles todas las variantes de racores.

Consideration: Remove O-rings before brazing!  
Please apply the standard brazing reulations!

Hinweis: O-Ringe vor dem Lötén entfernen!  
Bitte beachten Sie die allgemeinen Lötvorschriften!

Remarque: Enlever les joints toriques avant brasure.  
Brasage suivant recommandations générales.

Indicazione: Eliminare Gli-ring prima di saldare.  
Osservare le regole generali di saldatura prego!

Indicación: Desmontar las juntas tóricas antes de soldar.  
Observar las normas generales de soldadura, por favor!

Specification subject to change without notice